

Steam Distiller DS1G

Purification System

Pure, Distilled Water, It's that Simple

Easy to operate

You will love using our model DS1G Steam Distiller. Fill the stainless-steel boiler with tap water, place cover on unit and press the button. Shortly after you will have the purest possible distilled water.

Features:

- Rapid distilled water production: produces 4L of distilled water in 3.5 hours
- On/Off Switch: Start or stop condensation process at any time.




PN# DS1G



Phone - 800.233.0210

www.pennvet.com





1. Top body
2. Main body
3. Top body power cable
4. Top body socket
5. Power cord socket
6. ON/OFF Switch
7. Water Outlets
8. Water Container
9. Indicator Light
10. ON/OFF Switch

DS1G Water Distiller
Rated voltage: 110-120V
Rated frequency: 50-60 Hz
Rated power: 750W
Max capacity: 4 Liters
Amount of distillation: 1 Liter per hour

Accessory Items:



Kleenwise™ Distiller
 Cleaner and Descaler
 PN# KSD



Clean & Simple
 Ultrasonic Cleaning System
 PN#CSU1



Clean & Simple
 Ultrasonic Enzymatic Tablets
 PN#CS0064



Tuttnauer USA Co. Ltd.

25 Power Drive, Hauppauge, NY 11788

Tel: +800 624 5836, +631 737 4850, Fax: +631 737 0720

E-mail: info@tuttnauerUSA.com, www.tuttnauerUSA.com

Learn more about our promotions
 Visit: tuttnauerUSA.com/promotions/
 Learn from our experts.
 Visit our blog: tuttnauerUSA.com/blog/

